

## Aqua-Crosslinker 8482 Vetro

8482

Water-based crosslinker for glass coating for industrial and professional use

### PRODUCT DESCRIPTION

#### Product numbers

8482000210



#### General

Water-based special crosslinker for glass coating on the backside

#### Application area



Special crosslinker as adhesion promoter for water-based lacquers for glass coating.

For furniture and interior finishing.

### PROCESSING

#### Processing instructions

- Immediately after adding Aqua-Crosslinker 8482 Vetro (8482) to the paint component, blend in carefully.
- Please observe the respective technical data sheets of the blended products. The processing properties of the products are preserved.
- Any change in the processing sequence, environmental conditions, non-observance of instructions or the use of products not listed may have an unfavourable effect on the result.
- Please observe our **ARL 143 - Working guidelines for glass coating with furniture coatings**.

### ORDERING INFORMATION

#### Size of trading unit

1 kg, 5 kg, 10 kg

### FURTHER DETAILS

#### Durability / storage



Min. 1 year(s) in the original sealed containers.

Make sure the product is protected against moisture, direct sunlight, frost and high temperatures (above 30 °C).

Immediately seal the container to prevent humidity from penetrating.

---

## Safety information



Further information on the subject of safety during transport, storage and handling as well as disposal can be found in the relevant safety data sheet. The current version can be accessed on the Internet at **[www.adler-lacke.com](http://www.adler-lacke.com)**.

The product is only suitable for the industrial and professional use.

---